



★ KH10

Linear ball bearing

Schaeffler ID:
0003421730000

Linear ball bearings with preservative, not sealed, with relubrication facility

★ Preferred product

Technical information

Main Dimensions & Performance Data

F_w	10 mm	Diameter shaft
D	17 mm	Outer diameter
L	26 mm	Länge
C_{min}	510 N	load capacity dyn.
C_{0min}	370 N	load capacity stat.
C_{max}	590 N	load capacity dyn.
C_{0max}	520 N	load capacity stat.
	14 g	Weight

Mounting dimensions

J_{L4}	6 mm
N_2	2,5 mm

Additional information

VMKB_065	KH	Material name
----------	----	---------------

