



★ KH14

Linear ball bearing

Schaeffler ID:
0003421810000

Linear ball bearings with preservative, not sealed, with relubrication facility

★ Preferred product

Technical information

Main Dimensions & Performance Data

F_w	14 mm	Diameter shaft
D	21 mm	Outer diameter
L	28 mm	Länge
C_{min}	690 N	load capacity dyn.
C_{0min}	520 N	load capacity stat.
C_{max}	830 N	load capacity dyn.
C_{0max}	760 N	load capacity stat.
	19,89 g	Weight

Mounting dimensions

J_{L4}	6 mm
N_2	2,5 mm

Additional information

VMKB_065	KH	Material name
----------	----	---------------

