



★ KH16

Linear ball bearing

Schaeffler ID:
0003421900000

Linear ball bearings with preservative, not sealed, with relubrication facility

★ Preferred product

Technical information

Main Dimensions & Performance Data

F_w	16 mm	Diameter shaft
D	24 mm	Outer diameter
L	30 mm	Länge
C_{min}	890 N	load capacity dyn.
C_{0min}	620 N	load capacity stat.
C_{max}	1.060 N	load capacity dyn.
C_{0max}	910 N	load capacity stat.
	26,5 g	Weight

Mounting dimensions

J_{L4}	7 mm
N_2	2,5 mm

Additional information

VMKB_065	KH	Material name
----------	----	---------------

