



★ KH20

Linear ball bearing

Schaeffler ID:
0003422030000

Linear ball bearings with preservative, not sealed, with relubrication facility

★ Preferred product

Technical information

Main Dimensions & Performance Data

F_w	20 mm	Diameter shaft
D	28 mm	Outer diameter
L	30 mm	Länge
C_{min}	1.110 N	load capacity dyn.
C_{0min}	790 N	load capacity stat.
C_{max}	1.170 N	load capacity dyn.
C_{0max}	1.010 N	load capacity stat.
	31,75 g	Weight

Mounting dimensions

J_{L4}	7 mm
N_2	2,5 mm

Additional information

VMKB_065	KH	Material name
----------	----	---------------

