



## ★ KH30

Linear ball bearing

Schaeffler ID:  
0003422110000

Linear ball bearings with preservative, not sealed, with relubrication facility

★ Preferred product

## Technical information

### Main Dimensions & Performance Data

$F_w$	30 mm	Diameter shaft
D	40 mm	Outer diameter
L	50 mm	Länge
$C_{min}$	3.300 N	load capacity dyn.
$C_{0min}$	2.700 N	load capacity stat.
$C_{max}$	3.300 N	load capacity dyn.
$C_{0max}$	3.100 N	load capacity stat.
	92,44 g	Weight

### Mounting dimensions

$J_{L4}$	8 mm
$N_2$	2,5 mm

### Additional information

VMKB_065	KH	Material name
----------	----	---------------

