



★ KH40

Linear ball bearing

Schaeffler ID:
0003422200000

Linear ball bearings with preservative, not sealed, with relubrication facility

★ Preferred product

Technical information

Main Dimensions & Performance Data

F_w	40 mm	Diameter shaft
D	52 mm	Outer diameter
L	60 mm	Länge
C_{min}	5.300 N	load capacity dyn.
C_{0min}	4.450 N	load capacity stat.
C_{max}	5.300 N	load capacity dyn.
C_{0max}	4.950 N	load capacity stat.
	0,184 kg	Weight

Mounting dimensions

J_{L4}	9 mm
N_2	2,5 mm

Additional information

VMKB_065	KH	Material name
----------	----	---------------

