



★ KH50

Linear ball bearing

Schaeffler ID:
0003422460000

Linear ball bearings with preservative, not sealed, with relubrication facility

★ Preferred product

Technical information

Main Dimensions & Performance Data

F_w	50 mm	Diameter shaft
D	62 mm	Outer diameter
L	70 mm	Länge
C_{min}	6.800 N	load capacity dyn.
C_{0min}	6.300 N	load capacity stat.
C_{max}	6.800 N	load capacity dyn.
C_{0max}	7.000 N	load capacity stat.
	0,255 kg	Weight

Mounting dimensions

J_{L4}	9 mm
N_2	2,5 mm

Additional information

VMKB_065	KH	Material name
----------	----	---------------

