



## ★ GAY30-XL-NPP-B

Radial insert ball bearing


Schaeffler ID:  
0008802130000

★ Preferred product

Radial insert ball bearings GAY..-NPP-B, spherical outer ring, location by grub screws, P seals on both sides

X-life

### Technical information



### Main Dimensions & Performance Data

d	30 mm	Bore diameter
D <sub>SP</sub>	62 mm	Outside diameter
B	30 mm	Width
n <sub>G Grease</sub>	13.800 1/min	Limiting speed for grease lubrication
C <sub>r</sub>	19.500 N	Basic dynamic load rating, radial
C <sub>0r</sub>	11.300 N	Basic static load rating, radial
C <sub>ur</sub>	480 N	Fatigue load limit, radial
	0,25 kg	Weight

### Dimensions

C	18 mm	Width, outer ring
S	9 mm	Distance raceway
d <sub>1</sub>	39,4 mm	Rib diameter inner ring
d <sub>2</sub>	37,3 mm	Rib diameter sealing inner ring
C <sub>a</sub>	4,7 mm	Distance to lubrication hole
A	5,8 mm	Distance thread
W	3 mm	Width of flats

### Additional information

f <sub>0</sub>	13,8	Calculation factor
----------------	------	--------------------