

★ RNA4900-XL

Radial roller bearing


Schaeffler ID:
0506599360000

Radial roller bearing RNA..-XL

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	16,5 g	Weight

Main Dimensions & Performance Data

F_w	14 mm	Under roller diameter
D	22 mm	Outside diameter
B	13 mm	Width
C_r	9.600 N	Basic dynamic load rating, radial
C_{0r}	9.200 N	Basic static load rating, radial
C_{ur}	1.660 N	Fatigue load limit, radial
n_G	24.600 1/min	Limiting speed
$n_{G \text{ Grease}}$	14.800 1/min	Limiting speed for grease lubrication
n_{gr}	17.800 1/min	Reference speed

Dimensions

r_{\min}	0,3 mm	Minimum chamfer dimension
C	13 mm	Width, outer ring

Additional information

G14X22X3	Sealing ring
SD14X22X3	Sealing ring 2