



★ NA4922-XL

Needle roller bearing

Schaeffler ID:
0506616630000

Needle roller bearing NA49..-XL, single row, with inner ring, outer ring with 2 bords

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	2,085 kg	Weight

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	150 mm	Outside diameter
B	40 mm	Width
C_r	149.000 N	Basic dynamic load rating, radial
C_{0r}	290.000 N	Basic static load rating, radial
C_{ur}	48.000 N	Fatigue load limit, radial
n_G	3.700 1/min	Limiting speed
n_{gr}	2.330 1/min	Reference speed

Dimensions

F	125 mm	Raceway diameter inner ring
r_{\min}	1,1 mm	Minimum chamfer dimension
s	2 mm	Axial displacement