



★ NK14/20-XL

Needle roller bearing


Schaeffler ID:
0507533390000

Needle roller bearings NK, light series

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	25,6 g	Weight

Main Dimensions & Performance Data

F_w	14 mm	Under roller diameter
D	22 mm	Outside diameter
C	20 mm	Width, outer ring
C_r	14.500 N	Basic dynamic load rating, radial
C_{0r}	15.600 N	Basic static load rating, radial
C_{ur}	2.750 N	Fatigue load limit, radial
n_G	24.600 1/min	Limiting speed
n_{gr}	18.300 1/min	Reference speed

Dimensions

r_{\min}	0,3 mm	Minimum chamfer dimension
------------	--------	---------------------------

Additional information

G14X22X3	Sealing ring
SD14X22X3	Sealing ring 2