



★ NK15/16-XL

Needle roller bearing

Schaeffler ID:
0507534440000

Needle roller bearings NK, light series

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	21,5 g	Weight

Main Dimensions & Performance Data

F_w	15 mm	Under roller diameter
D	23 mm	Outside diameter
C	16 mm	Width, outer ring
C_r	12.100 N	Basic dynamic load rating, radial
C_{0r}	12.700 N	Basic static load rating, radial
C_{ur}	2.360 N	Fatigue load limit, radial
n_G	23.900 1/min	Limiting speed
n_{gr}	17.300 1/min	Reference speed

Dimensions

r_{\min}	0,3 mm	Minimum chamfer dimension
------------	--------	---------------------------

Additional information

	G15X23X3	Sealing ring
	SD15X23X3	Sealing ring 2