



★ NK85/25-XL

Needle roller bearing

Schaeffler ID:
0507546610000

Needle roller bearings NK, light series

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,004 kg	Weight

Main Dimensions & Performance Data

F_w	85 mm	Under roller diameter
D	105 mm	Outside diameter
C	25 mm	Width, outer ring
C_r	78.000 N	Basic dynamic load rating, radial
C_{0r}	123.000 N	Basic static load rating, radial
C_{ur}	22.100 N	Fatigue load limit, radial
n_G	5.400 1/min	Limiting speed
n_{gr}	3.550 1/min	Reference speed

Dimensions

r_{\min}	1 mm	Minimum chamfer dimension
------------	------	---------------------------