



★ NKI40/30-TV-XL

Needle roller bearing



Schaeffler ID:
0507622810000

Needle roller bearings NKI, light series

★ Preferred product

X-life

Technical information



Temperature range

T_{\min}	-20 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,206 kg	Weight

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	55 mm	Outside diameter
B	30 mm	Width
C_r	52.000 N	Basic dynamic load rating, radial
C_{0r}	103.000 N	Basic static load rating, radial
C_{ur}	19.500 N	Fatigue load limit, radial
n_G	10.200 1/min	Limiting speed
n_{gr}	5.400 1/min	Reference speed

Dimensions

F	45 mm	Raceway diameter inner ring
r_{\min}	0,3 mm	Minimum chamfer dimension
s	1 mm	Axial displacement