



## ★ NA4838-XL

Needle roller bearing

Schaeffler ID:  
0507685490000

Needle roller bearing NA..-XL, single row,  
with inner ring, outer ring with 2 bords

★ Preferred product

X-life

### Technical information



#### Temperature range

$T_{min}$	-30 °C	Operating temperature min.
$T_{max}$	120 °C	Operating temperature max.
	5,543 kg	Weight

#### Main Dimensions & Performance Data

d	190 mm	Bore diameter
D	240 mm	Outside diameter
B	50 mm	Width
$C_r$	255.000 N	Basic dynamic load rating, radial
$C_{0r}$	690.000 N	Basic static load rating, radial
$C_{ur}$	102.000 N	Fatigue load limit, radial
$n_G$	2.250 1/min	Limiting speed
$n_{gr}$	1.330 1/min	Reference speed

#### Dimensions

F	210 mm	Raceway diameter inner ring
$r_{min}$	1,5 mm	Minimum chamfer dimension
s	1,5 mm	Axial displacement