

**NKS50-XL**

Needle roller bearing

Schaeffler ID:
0507700710000

Needle roller bearings NKS, heavy series

X-life

Technical information

**Temperature range**

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,157 kg	Weight

Main Dimensions & Performance Data

F_w	50 mm	Under roller diameter
D	65 mm	Outside diameter
C	22 mm	Width, outer ring
C_r	48.000 N	Basic dynamic load rating, radial
C_{0r}	67.000 N	Basic static load rating, radial
C_{ur}	11.800 N	Fatigue load limit, radial
n_G	8.900 1/min	Limiting speed
n_{gr}	5.500 1/min	Reference speed

Dimensions

r_{\min}	1 mm	Minimum chamfer dimension
------------	------	---------------------------