



## ★ NKS55-XL

Needle roller bearing

Schaeffler ID:  
0507700800000

Needle roller bearings NKS, heavy series

★ Preferred product

X-life

### Technical information



#### Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.
	0,217 kg	Weight

#### Main Dimensions & Performance Data

$F_w$	55 mm	Under roller diameter
$D$	72 mm	Outside diameter
$C$	22 mm	Width, outer ring
$C_r$	51.000 N	Basic dynamic load rating, radial
$C_{0r}$	74.000 N	Basic static load rating, radial
$C_{ur}$	13.000 N	Fatigue load limit, radial
$n_G$	8.200 1/min	Limiting speed
$n_{gr}$	5.100 1/min	Reference speed

#### Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
------------	------	---------------------------