



★ LR608-2RSR

Track roller

Schaeffler ID:
0584419050000

Track roller LR6..-2RSR, single row, no plastic tyre

★ Preferred product

Technical information

Main Dimensions & Performance Data

D	24 mm	Outside diameter
d	8 mm	Bore diameter
C	7 mm	Height
C _{r w}	2.950 N	Basic dynamic load rating, radial
C _{0r w}	1.280 N	Basic static load rating, radial
C _{ur w}	64 N	Fatigue load limit, radial
n _{D G}	19.000 1/min	Speed on permanent grease lubrication
	0,016 kg	Weight

Dimensions

d ₂	10 mm	Diameter of thrust washer
r _{min}	0,3 mm	Minimum chamfer dimension
R	500 mm	Radius of outer ring outside profile