



IMAGE
COMING SOON



★ LR5306-2HRS-TVH-XL

Track roller

Schaeffler ID:
0838750260000

Track rollers LR50, double row, sealed on both sides

★ Preferred product

X-life

Technical information

Main Dimensions & Performance Data

D	80 mm	Outside diameter
d	30 mm	Bore diameter
C	30,2 mm	Height
C _{r w}	36.000 N	Basic dynamic load rating, radial
C _{0r w}	29.500 N	Basic static load rating, radial
C _{ur w}	1.520 N	Fatigue load limit, radial
n _{DG}	3.450 1/min	Speed on permanent grease lubrication
F _{r per}	27.000 N	Permissible dynamic load outer ring, radial
	0,67 kg	Weight

Dimensions

d ₂	44,4 mm	Diameter of thrust washer
r _{min}	1,1 mm	Minimum chamfer dimension
R	500 mm	Radius of outer ring outside profile