



★ K32X37X17


Needle roller cage assembly

Schaeffler ID:
0000025346063

Needle roller cage assembly K, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	140 °C	Operating temperature max.
	19,15 g	Weight

Main Dimensions & Performance Data

F_w	32 mm	Inner diameter of needle roller complement
E_w	37 mm	Outside diameter of needle roller complement
B_c	17 mm	Width
C_r	19.900 N	Basic dynamic load rating, radial
C_{0r}	35.500 N	Basic static load rating, radial
C_{ur}	4.600 N	Fatigue load limit, radial
n_G	14.200 1/min	Limiting speed
n_{gr}	7.900 1/min	Reference speed