



★ IR7X10X16-XL

Inner ring

Schaeffler ID:
0000201840000

Inner ring IR..-XL, cylindrical

★ Preferred product

X-life

Technical information



Main Dimensions & Performance Data

d	7 mm	Bore diameter
F	10 mm	Raceway diameter inner ring
B	16 mm	Width
	-0,007 mm	Raceway diameter upper tolerance
	-0,023 mm	Raceway diameter lower tolerance
r _{min}	0,3 mm	Minimum chamfer dimension
	4,8 g	Weight