



★ IR25X30X20,5-XL

Inner ring

Schaeffler ID:
0000216280000

Inner ring IR..-XL, cylindrical

★ Preferred product

X-life

Technical information



Main Dimensions & Performance Data

d	25 mm	Bore diameter
F	30 mm	Raceway diameter inner ring
B	20,5 mm	Width
	0 mm	Raceway diameter upper tolerance
	-0,012 mm	Raceway diameter lower tolerance
r _{min}	0,3 mm	Minimum chamfer dimension
	33,7 g	Weight

Mounting dimensions

	1	Number of lubrication holes
--	---	-----------------------------