

★ K60X68X25



Needle roller cage assembly

Schaeffler ID:
0000385046063

Needle roller cage assembly K, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	140 °C	Operating temperature max.
	89,22 g	Weight

Main Dimensions & Performance Data

F_w	60 mm	Inner diameter of needle roller complement
E_w	68 mm	Outside diameter of needle roller complement
B_c	25 mm	Width
C_r	53.000 N	Basic dynamic load rating, radial
C_{0r}	111.000 N	Basic static load rating, radial
C_{ur}	15.500 N	Fatigue load limit, radial
n_G	7.700 1/min	Limiting speed
n_{gr}	4.350 1/min	Reference speed