



## ★ K30X37X18


### Needle roller cage assembly

Schaeffler ID:  
0000732296063

Needle roller cage assembly K, single row

★ Preferred product

## Technical information



### Temperature range

$T_{min}$	-30 °C	Operating temperature min.
$T_{max}$	140 °C	Operating temperature max.
	29,6 g	Weight

### Main Dimensions & Performance Data

$F_w$	30 mm	Inner diameter of needle roller complement
$E_w$	37 mm	Outside diameter of needle roller complement
$B_c$	18 mm	Width
$C_r$	26.000 N	Basic dynamic load rating, radial
$C_{0r}$	38.500 N	Basic static load rating, radial
$C_{ur}$	5.400 N	Fatigue load limit, radial
$n_G$	14.600 1/min	Limiting speed
$n_{gr}$	8.000 1/min	Reference speed