

★ K28X33X17



Needle roller cage assembly

Schaeffler ID:
0000753536063

Needle roller cage assembly K, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	140 °C	Operating temperature max.
	16,89 g	Weight

Main Dimensions & Performance Data

F_w	28 mm	Inner diameter of needle roller complement
E_w	33 mm	Outside diameter of needle roller complement
B_c	17 mm	Width
C_r	19.700 N	Basic dynamic load rating, radial
C_{0r}	33.500 N	Basic static load rating, radial
C_{ur}	4.350 N	Fatigue load limit, radial
n_G	16.100 1/min	Limiting speed
n_{gr}	8.700 1/min	Reference speed