



★ K52X57X12



Needle roller cage assembly

Schaeffler ID:
0000886176063

Needle roller cage assembly K, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	140 °C	Operating temperature max.
	21,2 g	Weight

Main Dimensions & Performance Data

F_w	52 mm	Inner diameter of needle roller complement
E_w	57 mm	Outside diameter of needle roller complement
B_c	12 mm	Width
C_r	18.000 N	Basic dynamic load rating, radial
C_{0r}	36.500 N	Basic static load rating, radial
C_{ur}	4.700 N	Fatigue load limit, radial
n_G	9.000 1/min	Limiting speed
n_{gr}	5.400 1/min	Reference speed