



## ★ K14X18X17

### Needle roller cage assembly

Schaeffler ID:  
0000952496063

Needle roller cage assembly K, single row

★ Preferred product

## Technical information



### Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	140 °C	Operating temperature max.
	8,6 g	Weight

### Main Dimensions & Performance Data

$F_w$	14 mm	Inner diameter of needle roller complement
$E_w$	18 mm	Outside diameter of needle roller complement
$B_c$	17 mm	Width
$C_r$	10.800 N	Basic dynamic load rating, radial
$C_{0r}$	14.400 N	Basic static load rating, radial
$C_{ur}$	1.920 N	Fatigue load limit, radial
$n_G$	25.000 1/min	Limiting speed
$n_{gr}$	17.300 1/min	Reference speed