



★ K25X29X17

Needle roller cage assembly

Schaeffler ID:
0001822736063

Needle roller cage assembly K, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	140 °C	Operating temperature max.
	14,42 g	Weight

Main Dimensions & Performance Data

F_w	25 mm	Inner diameter of needle roller complement
E_w	29 mm	Outside diameter of needle roller complement
B_c	17 mm	Width
C_r	14.900 N	Basic dynamic load rating, radial
C_{0r}	26.000 N	Basic static load rating, radial
C_{ur}	3.500 N	Fatigue load limit, radial
n_G	18.100 1/min	Limiting speed
n_{gr}	10.200 1/min	Reference speed