



★ K60X65X20

Needle roller cage assembly

Schaeffler ID:
0002799196063

Needle roller cage assembly K, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	140 °C	Operating temperature max.
	52,8 g	Weight

Main Dimensions & Performance Data

F_w	60 mm	Inner diameter of needle roller complement
E_w	65 mm	Outside diameter of needle roller complement
B_c	20 mm	Width
C_r	29.500 N	Basic dynamic load rating, radial
C_{0r}	72.000 N	Basic static load rating, radial
C_{ur}	9.500 N	Fatigue load limit, radial
n_G	7.800 1/min	Limiting speed
n_{gr}	4.750 1/min	Reference speed