



★ K47X52X17

Needle roller cage assembly

Schaeffler ID:
0006220526063

Needle roller cage assembly K, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	140 °C	Operating temperature max.
	35,3 g	Weight

Main Dimensions & Performance Data

F_w	47 mm	Inner diameter of needle roller complement
E_w	52 mm	Outside diameter of needle roller complement
B_c	17 mm	Width
C_r	23.300 N	Basic dynamic load rating, radial
C_{0r}	49.000 N	Basic static load rating, radial
C_{ur}	6.300 N	Fatigue load limit, radial
n_G	9.900 1/min	Limiting speed
n_{gr}	5.800 1/min	Reference speed