

## ★ K85X92X20



### Needle roller cage assembly

Schaeffler ID:  
0006291386063

Needle roller cage assembly K, single row

★ Preferred product

## Technical information



### Temperature range

$T_{min}$	-30 °C	Operating temperature min.
$T_{max}$	140 °C	Operating temperature max.
	0,104 kg	Weight

### Main Dimensions & Performance Data

$F_w$	85 mm	Inner diameter of needle roller complement
$E_w$	92 mm	Outside diameter of needle roller complement
$B_c$	20 mm	Width
$C_r$	44.500 N	Basic dynamic load rating, radial
$C_{0r}$	108.000 N	Basic static load rating, radial
$C_{ur}$	15.400 N	Fatigue load limit, radial
$n_G$	5.500 1/min	Limiting speed
$n_{gr}$	3.450 1/min	Reference speed