



★ K35X42X30


Needle roller cage assembly

Schaeffler ID:
0013737226063

Needle roller cage assembly K, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	140 °C	Operating temperature max.
	66 g	Weight

Main Dimensions & Performance Data

F_w	35 mm	Inner diameter of needle roller complement
E_w	42 mm	Outside diameter of needle roller complement
B_c	30 mm	Width
C_r	39.000 N	Basic dynamic load rating, radial
C_{0r}	68.000 N	Basic static load rating, radial
C_{ur}	9.500 N	Fatigue load limit, radial
n_G	12.700 1/min	Limiting speed
n_{gr}	7.200 1/min	Reference speed