



★ K25X32X16


Needle roller cage assembly

Schaeffler ID:
0027098806063

Needle roller cage assembly K, single row

★ Preferred product

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	140 °C	Operating temperature max.
	22,8 g	Weight

Main Dimensions & Performance Data

F_w	25 mm	Inner diameter of needle roller complement
E_w	32 mm	Outside diameter of needle roller complement
B_c	16 mm	Width
C_r	20.800 N	Basic dynamic load rating, radial
C_{0r}	27.500 N	Basic static load rating, radial
C_{ur}	3.750 N	Fatigue load limit, radial
n_G	17.200 1/min	Limiting speed
n_{gr}	9.400 1/min	Reference speed