

QL 3 SAK2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

| | |
|------------|--|
| Version | SAK Series, Cross-connector, for cross-connection link, Number of poles: 3 |
| Order No. | 0156000000 |
| Type | QL 3 SAK2.5 |
| GTIN (EAN) | 4008 190027360 |
| Qty. | 100 pc(s). |

Creation date March 1, 2023 3:16:20 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

QL 3 SAK2.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.6 mm | Depth (inches) | 0.024 inch |
| Height | 6 mm | Height (inches) | 0.236 inch |
| Width | 17.2 mm | Width (inches) | 0.677 inch |
| Net weight | 0.39 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|--------|--------|------|
| Material | Copper | Colour | grey |
|----------|--------|--------|------|

System specifications

| | |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | when screwed in | | |

Cross-connector

| | | | |
|-------------------------------------|------|-----------------------|-----------------|
| Number of cross-connected terminals | 3 | Rated current, 2-pole | 41 A |
| Rated current, multi-pole | 41 A | Type | Cross-connector |

Dimensions

| | |
|-----------------|------|
| Pitch in mm (P) | 6 mm |
|-----------------|------|

General

| | | | |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 3 |
|---------------------|-----------------|-----------------|---|

Rating data

| | |
|---------------|------|
| Rated current | 99 A |
|---------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ECLASS 9.0 | 27-14-11-40 |
| ECLASS 9.1 | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 | ECLASS 12.0 | 27-14-11-40 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Creation date March 1, 2023 3:16:20 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

QL 3 SAK2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Downloads**

| | |
|---|---|
| Approval/Certificate/Document of Conformity | EAC certificate |
| Engineering Data | WSCAD |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
