

**AD 4 SAK10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

**General ordering data**

Version	SAK Series, cover plate, yellow, 25 mm
Order No.	<a href="#">0178600000</a>
Type	AD 4 SAK10
GTIN (EAN)	4008 190068288
Qty.	50 pc(s).

Creation date February 28, 2023 8:25:44 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## AD 4 SAK10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	1 mm	Depth (inches)	0.039 inch
Height	39.6 mm	Height (inches)	1.559 inch
Width	25 mm	Width (inches)	0.984 inch
Net weight	1.22 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

## Material data

Material	PVC	Colour	yellow
UL 94 flammability rating	HB		

## System specifications

Version	End and intermediate plate
---------	----------------------------

## Additional technical data

Installation advice	Direct mounting	Snap-on	No
---------------------	-----------------	---------	----

## General

Installation advice	Direct mounting
---------------------	-----------------

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>