

**AP SAKS1+3 KRG/DB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

Version	SAK Series, End plate, 3 mm, dark beige, Direct mounting
Order No.	<a href="#">0191300000</a>
Type	AP SAKS1+3 KRG/DB
GTIN (EAN)	4008 190099763
Qty.	20 pc(s).

Creation date March 6, 2023 6:41:49 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## AP SAKS1+3 KRG/DB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	36 mm	Depth (inches)	1.417 inch
Height	54 mm	Height (inches)	2.126 inch
Width	3 mm	Width (inches)	0.118 inch
Net weight	7.75 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

### Material data

Material	KrG	Colour	dark beige
UL 94 flammability rating	V-0		

### System specifications

Version	End plate
---------	-----------

### Additional technical data

Installation advice	Direct mounting	Snap-on	Yes
---------------------	-----------------	---------	-----

### General

Installation advice	Direct mounting
---------------------	-----------------

### Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ECLASS 9.1	27-14-11-33
ECLASS 10.0	27-14-11-33	ECLASS 11.0	27-14-11-33
ECLASS 12.0	27-14-11-33		

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>