

G 25/6.30A/F GN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

For protection against overcurrent, we offer cartridge fuse with dimensions 5x25 mm in sizes from 250 mA to 6.3 A.

General ordering data

Version	Active components, Fuse
Order No.	0192900000
Type	G 25/6.30A/F GN
GTIN (EAN)	4008 190 13546 1
Qty.	10 pc(s).

G 25/6.30A/F GN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	5 mm	Depth (inches)	0.197 inch
Height	25 mm	Height (inches)	0.984 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	1.4 g		

Material data

Colour	Light Grey
--------	------------

System specifications

Version	Fuse accessories
---------	------------------

Fuse cartridges

Cartridge fuse	G-Si. 5 x 25	Characteristics	quick-acting
Colour	Light Grey	Colour of the indicator	green
Current	6.3 A	Melting integral	170 A ² s
Optical function display	Yes	Power output (@ 1.5 In)	1.8 W
Rated breaking capacity	1.5 kA	Version	Fuse accessories
Voltage drop	160 mV		

Rating data

Rated voltage	250 V	Rated current	6.3 A
---------------	-------	---------------	-------

Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ECLASS 9.0	27-14-20-01
ECLASS 9.1	27-14-20-01	ECLASS 10.0	27-14-20-01
ECLASS 11.0	27-14-20-01	ECLASS 12.0	27-14-20-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	