

QL 3 SAK6N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 3
Order No.	0194400000
Type	QL 3 SAK6N
GTIN (EAN)	4008 19006335 1
Qty.	50 pc(s).

Creation date February 20, 2023 4:06:16 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

QL 3 SAK6N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	1 mm	Depth (inches)	0.039 inch
Height	6 mm	Height (inches)	0.236 inch
Width	21.8 mm	Width (inches)	0.858 inch
Net weight	0.82 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Copper	Colour	grey
----------	--------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	3	Rated current, 2-pole	57 A
Rated current, multi-pole	57 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	7.9 mm
-----------------	--------

General

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Approvals

Approvals



ROHS	Conform
------	---------

Creation date February 20, 2023 4:06:17 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

Data sheet**QL 3 SAK6N**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Downloads**

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	
