

EWK 1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | |
|------------|-----------------------------|
| Version | Accessories, End bracket |
| Order No. | 0206 160000 |
| Type | EWK 1 |
| GTIN (EAN) | 4008 190080020 |
| Qty. | 50 pc(s). |

EWK 1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 31 mm | Depth (inches) | 1.22 inch |
| Height | 27 mm | Height (inches) | 1.063 inch |
| Width | 9 mm | Width (inches) | 0.354 inch |
| Net weight | 4.34 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|---------------------------|-------|--------|-------|
| Material | Wemid | Colour | beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|---------|-------------------|------|-------|
| Version | For the terminals | Rail | TS 32 |
|---------|-------------------|------|-------|

Additional technical data

| | | | |
|---------------------|-----------------|-----------|------------------|
| Installation advice | Direct mounting | Interlock | for screw fixing |
| Type of mounting | when screwed in | | |

Conductors for clamping (rated connection)

| | | | |
|-------------------------|------|-------------------------|--------|
| Tightening torque, max. | 1 Nm | Tightening torque, min. | 0.5 Nm |
|-------------------------|------|-------------------------|--------|

Dimensions

| | |
|--------------|---------|
| TS 32 offset | 13.5 mm |
|--------------|---------|

General

| | | | |
|---------------------|-----------------|------|-------|
| Installation advice | Direct mounting | Rail | TS 32 |
|---------------------|-----------------|------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001041 | ETIM 7.0 | EC001041 |
| ETIM 8.0 | EC001041 | ECLASS 9.0 | 27-14-11-35 |
| ECLASS 9.1 | 27-14-11-35 | ECLASS 10.0 | 27-14-11-35 |
| ECLASS 11.0 | 27-14-11-35 | ECLASS 12.0 | 27-14-11-35 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

EWK 1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Downloads**

| | |
|-----------------------------|-----------------------------------------------------------------------------------|
| Engineering Data | CAD data – 04520_EWK_1_DXF.dxf CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| Product Change Notification | Technical Change EN Technical Change DE |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |