

CLI C 02-3 GE/SW F MP

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, yellow |
| Order No. | 0252111647 |
| Type | CLI C 02-3 GE/SW F MP |
| GTIN (EAN) | 4008190151492 |
| Qty. | 200 pc(s). |

CLI C 02-3 GE/SW F MP

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 3.5 mm | Depth (inches) | 0.138 inch |
| Height | 3 mm | Height (inches) | 0.118 inch |
| Width | 3.4 mm | Width (inches) | 0.134 inch |
| Net weight | 0.03 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|--|--------------------|-----------------------------------|--|
| Colour | yellow | Colour of printing | black |
| Halogen | Yes | Material | PVC, soft, without Cadmium |
| Material colour according to resistance code | 4 | Number of markers per combination | 1 Component part = Conductor and cable markers |
| Operating temperature range | -30...80 °C | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -30 °C | Orientation of print | horizontal |
| Printed characters | Upper-case letters | Printing | F |
| Printing method | hot-embossing | Recommended industries | Process, Machinery |
| Type of printing | Standard | UL 94 flammability rating | V-0 |
| Version | MultiPack | Width | 3.4 mm |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|----------------------------------|---------------------------|
| Conductor O.D. | 1.3 - 3 mm | Conductor O.D., max. | 3 mm |
| Conductor O.D., min. | 1.3 mm | Conductor cross-section, max. | 1.5 mm ² |
| Conductor cross-section, min. | 0.2 mm ² | Cross-section for connected wire | 0.2 - 1.5 mm ² |
| Halogen | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | WSCAD |
| Product Change Notification | PCN CableLine_DE PCN CableLine_EN |
| Catalogues | Catalogues in PDF-format |

CLI C 02-3 GE/SW F MP

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Drawings



Similar to illustration