

VH 8/4.9/3.3 SAK2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
www.weidmueller.com

Product image



Similar to illustration

General ordering data

Version	SAK Series, Connecting sleeve, for cross-connection link, Number of poles:
Order No.	0266700000
Type	VH 8/4.9/3.3 SAK2.5
GTIN (EAN)	4008 190152031
Qty.	100 pc(s).

VH 8/4.9/3.3 SAK2.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	8 mm	Depth (inches)	0.315 inch
Height	4.9 mm	Height (inches)	0.193 inch
Width	4.9 mm	Width (inches)	0.193 inch
Diameter	4.9 mm	Net weight	0.69 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Copper	Colour	grey
----------	--------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	1	Type	Cross-connector
-------------------------------------	---	------	-----------------

Dimensions

Diameter	4.9 mm
----------	--------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format