

**VH 17/8/5 SAK35****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image****General ordering data**

Version	SAK Series, Connecting sleeve, for cross-connection link, Number of poles:
Order No.	<a href="#">0267000000</a>
Type	VH 17/8/5 SAK35
GTIN (EAN)	4008190146986
Qty.	50 pc(s).

## VH 17/8/5 SAK35

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	17 mm	Depth (inches)	0.669 inch
Height	8 mm	Height (inches)	0.315 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	3.2 g		

## Temperatures

Storage temperature -25 °C...55 °C

## Material data

Material Cu Zn Colour grey

## System specifications

Version for cross-connection link

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

## Cross-connector

Number of cross-connected terminals	1	Type	Cross-connector
-------------------------------------	---	------	-----------------

## General

Installation advice Direct mounting

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	73c55621-8329-401d-bde2-7fd78e0e60e4

## Approvals

ROHS Conform

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>