

DKSUE NSCH/ESCH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Building installation wiring**

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

General ordering data

Version	Accessories, Druckstück, Miscellaneous
Order No.	0280100000
Type	DKSUE NSCH/ESCH
GTIN (EAN)	4008190036348
Qty.	100 pc(s).

Creation date February 28, 2023 10:48:52 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

DKSUE NSCH/ESCH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	7.7 mm	Depth (inches)	0.303 inch
Height	12.5 mm	Height (inches)	0.492 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	1.326 g		

Temperatures

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	180 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version	Miscellaneous
---------	---------------

Additional technical data

Explosion-tested version	No	Type of fixing	when screwed in
--------------------------	----	----------------	-----------------

Dimensions

Pitch in mm (P)	13.5 mm
-----------------	---------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	