

H0,5/6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

General ordering data

Version	Wire-end ferrule, Standard, 6 mm, 6 mm, No
Order No.	0282600000
Type	H0,5/6
GTIN (EAN)	4008190184025
Qty.	1,000 pc(s).
Packaging	loose

Creation date February 15, 2023 4:56:14 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

H0,5/6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 0.029 g

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Collar diameter (D2)	2.1 mm	Conductor cross-section	0.5 mm ²
Contact surface diameter (D1)	1 mm	Contact surface length (L2)	6 mm
L1 in mm	6 mm	Stripping length	6 mm
Wire connection cross section AWG, max.	AWG 20		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

H0,5/6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

