

**VP 9-MS65****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|            |   |
|------------|---|
| Version    | VPMS (blanking plug in brass), Blanking plug, in closed state, PG 9, 5 mm, Brass, nickel-plated |
| Order No.  | <a href="#">0294700000</a>  |
| Type       | VP 9-MS65   |
| GTIN (EAN) | 4008 190005887  |
| Qty.       | 100 Stück   |

## VP 9-MS65

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |                      |            |
|------------|--------|----------------------|------------|
| Height     | 8 mm   | Height (inches)      | 0.315 inch |
| Length     | 8 mm   | Length (inches)      | 0.315 inch |
| Diameter   | 18 mm  | Wall thickness, max. | 4 mm       |
| Net weight | 4.45 g |                      |            |

### Temperatures

|                             |                 |                             |        |
|-----------------------------|-----------------|-----------------------------|--------|
| Operating temperature       | -40 °C...100 °C | Operating temperature, min. | -40 °C |
| Operating temperature, max. | 100 °C          |                             |        |

### General information

|                                   |                        |                                   |         |
|-----------------------------------|------------------------|-----------------------------------|---------|
| Cable glands                      | PG                     | Diameter of sealing ring          | 15.2 mm |
| External thread                   | PG 9                   | Halogen                           | No      |
| Head diameter                     | 18 mm                  | Length of thread                  | 5 mm    |
| Material                          | Brass, nickel-plated   | O-Ring                            | NBR     |
| Operating temperature range, max. | 100 °C                 | Operating temperature range, min. | -40 °C  |
| Protection degree                 | IP68 - 5 bar (30 min.) | Sealing                           | NBR     |
| Silicone                          | No                     |                                   |         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000451    | ETIM 7.0    | EC000451    |
| ETIM 8.0    | EC000451    | ECLASS 9.0  | 27-14-44-25 |
| ECLASS 9.1  | 27-14-44-33 | ECLASS 10.0 | 27-14-44-25 |
| ECLASS 11.0 | 27-14-44-25 | ECLASS 12.0 | 27-14-08-05 |

### Environmental Product Compliance

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203 |

### Approvals

Approvals



ROHS Conform

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">WSCAD, EPLAN</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |

**VP 9-MS65**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

