

VP 9-K54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|---|
| Version | VPK (blanking plug in plastic), Blanking plug, in closed state, PG 9, 5 mm, IP65, Polyamid 6 (PA6 - GF30) |
| Order No. | 0294760000 |
| Type | VP 9-K54 |
| GTIN (EAN) | 4008190105884 |
| Qty. | 100 Stück |

Erstellungs-Datum May 26, 2023 4:18:02 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

VP 9-K54

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|----------------------|------------|
| Length | 9.5 mm | Length (inches) | 0.374 inch |
| Diameter | 15.2 mm | Wall thickness, max. | 4 mm |
| Net weight | 0.97 g | | |

Temperatures

| | | | |
|-----------------------------|-----------------|-----------------------------|--------|
| Operating temperature | -40 °C...100 °C | Operating temperature, min. | -40 °C |
| Operating temperature, max. | 100 °C | | |

General information

| | | | |
|-----------------------------------|-------------------------|-----------------------------------|---------|
| Cable glands | PG | Diameter of sealing ring | 15.2 mm |
| External thread | PG 9 | Halogen | No |
| Head diameter | 19 mm | Length of thread | 5 mm |
| Material | Polyamid 6 (PA6 - GF30) | Operating temperature range, max. | 100 °C |
| Operating temperature range, min. | -40 °C | Protection degree | IP54 |
| Protection degree with GWDR | IP65 | UL 94 flammability rating | V-2 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000451 | ETIM 7.0 | EC000451 |
| ETIM 8.0 | EC000451 | ECLASS 9.0 | 27-14-44-25 |
| ECLASS 9.1 | 27-14-44-33 | ECLASS 10.0 | 27-14-44-25 |
| ECLASS 11.0 | 27-14-44-25 | ECLASS 12.0 | 27-14-08-05 |

Approvals

Approvals



ROHS

Conform

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

VP 9-K54

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

