

## H25,0/30 BR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Version	Wire-end ferrule, Standard, 18 mm, 16 mm, brown
Order No.	<a href="#">0317000000</a>
Type	H25,0/30 BR
GTIN (EAN)	4008190158231
Qty.	50 pc(s).
Packaging	loose

Creation date February 20, 2023 2:58:49 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

**H25,0/30 BR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 1.12 g

**Technical data**

Description of article	Wire end ferrule with plastic collar, brown	Version	Standard
------------------------	---	---------	----------

**Wire-end ferrules**

Collar diameter (D2)	11.2 mm	Colour code	Weidmüller
Conductor cross-section	25 mm <sup>2</sup>	Contact surface diameter (D1)	7.3 mm
Contact surface length (L2)	16 mm	L1 in mm	30 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 030 A
Plastic collar thickness (S2)	0.4 mm	Stripping length	18 mm
Wire connection cross section AWG, max.	AWG 3		

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**H25,0/30 BR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

