

VH 30.5/11/5.5 SAK70

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image



Similar to illustration

General ordering data

| | |
|-----------------|--|
| Version | SAK Series, Connecting sleeve, for cross-connection link, Number of poles: |
| Order No. | 0345500000 |
| Type | VH 30.5/11/5.5 SAK70 |
| GTIN (EAN) | 4008190100698 |
| Qty. | 20 pc(s). |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2022-07-29 |

VH 30.5/11/5.5 SAK70

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|----------|---------|-----------------|------------|
| Depth | 30.5 mm | Depth (inches) | 1.201 inch |
| Height | 11 mm | Height (inches) | 0.433 inch |
| Width | 11 mm | Width (inches) | 0.433 inch |
| Diameter | 11 mm | Net weight | 18.3 g |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|-------|--------|------|
| Material | Cu Zn | Colour | grey |
|----------|-------|--------|------|

System specifications

| | |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | when screwed in | | |

Cross-connector

| | | | |
|-------------------------------------|---|------|-----------------|
| Number of cross-connected terminals | 1 | Type | Cross-connector |
|-------------------------------------|---|------|-----------------|

Dimensions

| | |
|----------|-------|
| Diameter | 11 mm |
|----------|-------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| ETIM 8.0 | EC002848 | ECLASS 9.0 | 27-14-11-92 |
| ECLASS 9.1 | 27-14-11-92 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 | ECLASS 12.0 | 27-14-11-92 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 73c55621-8329-401d-bde2-7fd78e0e60e4 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Data sheet**VH 30.5/11/5.5 SAK70****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.comwww.weidmueller.com**Technical data****Downloads**

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |