

**Q 3 SAKD2.5N**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 3
Order No.	<a href="#">0367900000</a>
Type	Q 3 SAKD2.5N
GTIN (EAN)	4008190176778
Qty.	50 pc(s).

Creation date March 2, 2023 10:13:15 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

**Q 3 SAKD2.5N**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	20.5 mm	Depth (inches)	0.807 inch
Height	6 mm	Height (inches)	0.236 inch
Width	14.6 mm	Width (inches)	0.575 inch
Net weight	4.08 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	CuSn	Colour	grey
----------	------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Cross-connector**

Number of cross-connected terminals	3	Rated current, 2-pole	24 A
Rated current, multi-pole	24 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	5 mm
-----------------	------

**General**

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

**Rating data**

Rated current	24 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	15ca0fd7-d890-4b34-9652-12e72c65fa2d

**Q 3 SAKD2.5N**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of  
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)