

**Q 10 SAK2.5****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 10
Order No.	<a href="#">0368700000</a>
Type	Q 10 SAK2.5
GTIN (EAN)	4008190107796
Qty.	20 pc(s).

**Q 10 SAK2.5**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	20.5 mm	Depth (inches)	0.807 inch
Height	6 mm	Height (inches)	0.236 inch
Width	60.6 mm	Width (inches)	2.386 inch
Net weight	17.5 g		

**Temperatures**

Storage temperature -25 °C...55 °C

**Material data**

Material CuSn Colour grey

**System specifications**

Version for cross-connection link

**Additional technical data**Explosion-tested version No Installation advice Direct mounting  
Type of fixing when screwed in**Cross-connector**Number of cross-connected terminals 10 Rated current, 2-pole 41 A  
Rated current, multi-pole 41 A Type Cross-connector**Dimensions**

Pitch in mm (P) 6 mm

**General**

Installation advice Direct mounting Number of poles 10

**Rating data**

Rated current 24 A

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**Approvals**

Approvals



ROHS Conform

Creation date March 3, 2023 1:03:20 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

**Q 10 SAK2.5****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Downloads**Approval/Certificate/Document of  
Conformity[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)